



DSE 280 Intec

- For effective sanding of edges and corners
- Patented, rotating base plate for optimum utilisation of the edges of the sanding paper
- Dust-proof ball bearings for long service life of the machine
- Robust oscillation sleeve and base plate holder made from die-cast aluminium for a long service life
- Vario (V)-Electronics for working at customised orbital frequencies to suit various application materials
- Thumbwheel for preselection of the orbital frequency
- Easy change of sanding sheet with hook and loop base-plate
- Dust cartridge with filter for working without connecting to a vacuum cleaner
- Convenient handling thanks to slim design
- Compact design aids access when working in difficult to reach areas
- Extraction possibility by means of connecting to an all-purpose vacuum cleaner via an adapter (accessory)

Order no.	600317500
EAN code	4007430151360
Base plate, dimensions from corner to corner	93 mm / 3 5/8 "
Rated input power	280 W
Orbital frequency with no load	14000 - 22000 rpm
Orbit diameter	1.8 mm / 1/16 "
Weight (without power cable)	1.3 kg / 2.9 lbs
Cable length	2.6 m / 9 ft

Scope of delivery

Special lamellar base plate, Hexagonal wrench, Plastic carry case