



WEVA 15-125 Quick with speed control, quick-locking nut

- Highest service life for extreme applications: robust, powerful angle grinder with speed control and greatest power density in its class for quick work progress
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Low-vibration side handle Metabo VibraTech (MVT)
- Best anti-vibration system: integrated auto-balancer for up to 50% less hand-arm vibrations, longer service life of the machine and up to twice the service life of the grinding wheels
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Electronic overload protection, soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

| Order no. | 600496000 |
|------------------------------|--------------------|
| EAN code | 4007430246158 |
| Disc-Ø | 125 mm // 5 " |
| Rated input power | 1550 W |
| Output power | 940 W |
| No-load speed | 2800 - 11000 rpm |
| Speed at rated load | 11000 rpm |
| Torque | 3.5 Nm / 31 in-lbs |
| Spindle thread | M 14 |
| Handle circumference | 206 mm / 8 1/8 " |
| Weight (without power cable) | 2.5 kg / 5.5 lbs |
| Cable length | 4 m / 13 ft |

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Metabo VibraTech (MVT) side handle