



## BH 18 LTX BL 16

- Very lightweight, compact cordless hammer with brushless motor for low-fatigue drilling in any working position
- Maximum drill performance, efficiency and service life thanks to brushless technology and high-performance hammer action
- Rotary hammer with 2 functions: hammer drilling and drilling
- Metabo VibraTech (MVT): working, also continuously, in a low-fatigue manner whilst protecting the user's health
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Electronic safety shutdown of the motor for safe working in case the tool stops unexpectedly
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	600324850
EAN code	4061792191686
Battery voltage	18 V
Max. single blow energy (EP-TA)	1.3 J
Maximum impact rate	5250 bpm
Drill-Ø concrete with hammer drills	16 mm / 5/8 "
Drill-Ø masonry with core bits	68 mm / 2.6725 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	20 mm / 25/32 "
No-load speed	0 - 730 rpm
Bit retainer	SDS-plus
Weight without battery pack	1.6 kg / 3.5 lbs
Weight with battery pack	2 kg / 4.4 lbs

### Scope of delivery

Side handle, Drilling depth guide, without battery pack, without charger