



WEP 17-125 Quick

- Maximum productivity: 1,700 Watt angle grinder with the power of a large grinder and the compactness of a small one for quickest material removal on industrial applications
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Tacho Constamatic (TC) Full-wave Electronics: fast work progress by means of constant speed under load
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Low-vibration side handle Metabo VibraTech (MVT)
- Paddle switch with dead man function: safe to operate due to an ergonomically integrated switch
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Electronic overload protection, soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Order no.	600547000
EAN code	4061792176263
Disc-Ø	125 mm // 5 "
Rated input power	1700 W
Output power	1040 W
No-load speed	11000 rpm
Speed at rated load	11000 rpm
Torque	3.7 Nm / 33 in-lbs
Spindle thread	M 14
Handle circumference	197 mm / 7 3/4 "
Weight (without power cable)	2.5 kg / 5.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Metabo VibraTech (MVT) side handle