



## BAE 75 with Machine Stand

- Excellent sanding results thanks to powerful motor and precise belt path
- Fast and tool-free sanding belt change
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for working at customised speeds to suit the application material and belt speeds that remain almost constant, even under load
- Thumbwheel for preselection of belt speed
- With antistatic dust bag for working without connecting a vacuum cleaner
- Side handle for ideal machine guidance
- With machine stand for tool-free conversion for stationary use in a matter of seconds
- With length guide for exact guidance of the workpiece in stationary use
- Extraction possibility by means of connecting an all-purpose vacuum cleaner

Order no.	600375000
EAN code	4007430185655
Torque	12 Nm / 106 in-lbs
Sanding belt	75 x 533 mm // 3 x 21 "
Sanding belt supporting surface	85 x 150 mm // 3 3/8 x 6 "
Belt speed in idle	240 - 450 m/min
Rated input power	1010 W
Weight (without power cable)	4.9 kg / 10.8 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Dust bag, Side handle, Hexagonal wrench, Suction adapter, Length guide, Machine stand