



WEV 17-150 Quick with speed control, quick-locking nut

- Highest service life for extreme applications: robust, powerful angle grinder with speed control and greatest power density in its class for quick work progress
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Low-vibration side handle Metabo VibraTech (MVT)
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Electronic overload protection, soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Order no.	600473000
EAN code	4061792176218
Disc-Ø	150 mm // 6 "
Rated input power	1700 W
No-load speed	2800 - 10000 rpm
Speed at rated load	9600 rpm
Torque	4.3 Nm / 38.1 in-lbs
Spindle thread	M 14
Handle circumference	206 mm / 8 1/8 "
Weight (without power cable)	2.5 kg / 5.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Metabo VibraTech (MVT) side handle