



KHE 3251 with Metabo Quick change chuck

- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo Quick: quick change between SDS Plus hammer chuck and keyless chuck for drilling in wood and metal
- Metabo VibraTech (MVT): integrated damping system and side handle to reduce vibrations in order to protect the user's health
- Ergonomic housing shape for chiselling tasks without side handle
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Metabo Marathon-motor with dust protection for long service life
- High performance hammer action, precisely mounted in a housing made of aluminium alloy: long-lasting and robust
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Cable-protecting ball joint for optimal freedom of motion when working
- With metaBOX, the intelligent solution for transport and storage

Order no.	600659000
EAN code	4007430208705
Max. single blow energy (EP-TA)	3.1 J
Maximum impact rate	4470 bpm
Rated input power	800 W
Drill-Ø concrete with hammer drills	32 mm / 1 1/4 "
Drill-Ø masonry with core bits	82 mm / 3 1/4 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	35 mm / 1 3/8 "
No-load speed	0 - 1150 rpm
Speed at rated load	920 rpm
Bit retainer	SDS-plus
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	3.6 kg / 7.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

Hammer chuck for tools with SDS-plus shank end, Keyless chuck for tools with cylindrical shank, Metabo VibraTech (MVT) side handle, Drilling depth guide, metaBOX 165 L