



WBE 700

- Powerful angle drill for drilling in difficult to access areas
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Vario-Constamatic (VC)- Electronics for work with materials requiring customised speeds, which remain almost constant under load
- Thumbwheel for speed preselection

Order no.	600512000
EAN code	4007430083005
Rated input power	700 W
Output power	305 W
Drill Ø steel	10 mm // 3/8 "
Drill-Ø soft wood	25 mm // 1 "
No-load speed	850 - 2600 rpm
Speed at rated load	2300 rpm
Gears	1
Maximum torque	8 Nm // 71 in-lbs
Chuck capacity	1 - 10 mm // 1/32 - 3/8 "
Drill spindle thread	1/2 " - 20 UNF
Weight (without power cable)	2 kg / 4.4 lbs
Cable length	4 m / 13 ft

Scope of delivery

Geared chuck, Chuck key, Side handle