



UHE 2660-2 Quick with Metabo Quick change chuck

- Multi hammer with 4 functions: hammer drilling, drilling without impact in two speeds and chiselling
- Metabo Quick: quick change between SDS Plus hammer chuck and keyless chuck for drilling in wood and metal
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Thumbwheel for preselection of the speed and impact rate
- Two-speed gear unit: two drilling speeds for effective drilling in wood and metal
- Metabo Marathon-motor with dust protection for long service life
- High performance hammer action, precisely mounted in a housing made of aluminium alloy: long-lasting and robust
- Perfect ergonomics thanks to the centre of gravity being near the hand and optimised handle contour
- Bottom switch protected against damage and dust
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Lockable switch for comfortable working in continuous operation
- Cable-protecting ball joint for optimal freedom of motion when working
- With metaBOX, the intelligent solution for transport and storage

Order no.	600697500
EAN code	4007430306227
Max. single blow energy (EP-TA)	2.8 J
Maximum impact rate	4200 bpm
Rated input power	800 W
Drill-Ø concrete with hammer drills	26 mm / 1 1/32 "
Drill-Ø masonry with core bits	68 mm / 2 11/16 "
Drill Ø steel	13 / 6 mm // 1/2 / 1/4 "
Drill-Ø soft wood	32 / 28 mm // 1 1/4 / 1 3/32 "
No-load speed	0 - 1050 / 0 - 2500 rpm
Speed at rated load	790 / 1860 rpm
Bit retainer	SDS-plus
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	3.1 kg / 6.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

Hammer chuck for tools with SDS-plus shank end, Keyless chuck for tools with cylindrical shank, rubber-coated side handle, Drilling depth guide, metaBOX 145 L