



KHA 18 LTX BL 40

- Cordless hammer with SDS max holder for extremely powerful hammer drilling and chiselling - any time and anywhere
- Maximum drill performance, efficiency and service life thanks to brushless technology and high-performance hammer action
- Low-dust chiselling and drilling with external dust extraction ESA max (accessories)
- Combination hammer with 2 functions: hammer drilling and chiselling
- Metabo VibraTech (MVT): working, also continuously, in a low-fatigue manner whilst protecting the user's health
- High performance hammer action, precisely mounted in a housing made of aluminium alloy: long-lasting and robust
- Vario Constamatic (VTC) Electronics for drilling jobs in materials requiring customised speeds, which remain almost constant under load
- Optional reduction of speed and impact energy for working in softer materials
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- With attachment point for tool safety straps for working at great heights
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600752840
EAN code	4061792199934
Battery voltage	18 V
Max. single blow energy (EP-TA)	8.6 J
Maximum impact rate	3200 bpm
Drill-Ø concrete with hammer drills	40 mm / 1 9/16 "
Drill-Ø masonry with core bits	105 mm / 4 1/8 "
No-load speed	450 - 580 rpm
Bit retainer	SDS-max
Weight without battery pack	6.9 kg / 15.3 lbs
Weight with battery pack	7.9 kg / 17.5 lbs

Scope of delivery

rubber-coated side handle, Side handle, Drilling depth guide, Lubricant for tool shank end, Duster, Plastic carry case, without battery pack, without charger