



MHEV 5 BL

- High breaking performance thanks to maintenance-free brushless motor and high-performance hammer action
- Long service life thanks to brushless technology and robust aluminium die-cast housings of gear and motor
- Metabo VibraTech (MVT) with double dampening: Decoupled handle and impact-absorbing counter-oscillating weight actively reduce vibrations for healthy working also in continuous use.
- Ergonomically shaped, slim gripping area with large speed control trigger for comfortable working
- Easily accessible locking switch for chiselling in continuous mode
- Optional reduction of the impact energy for working in softer materials
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Overload protection: protects the motor from overheating
- Low-dust chiselling with external dust extraction ESA max (accessories)
- The adjustable front handle can be rotated 360° and the angle adjusted for an optimum working position

Order no.	600769500
EAN code	4061792002678
Max. single blow energy (EP-TA)	8.7 J
Maximum impact rate	2900 bpm
Rated input power	1150 W
Bit retainer	SDS-max
Weight (without power cable)	7.9 kg / 17.4 lbs
Cable length	6 m / 236 7/32 "

Scope of delivery

Side handle, Front handle, Lubricant for tool shank end, Duster, Plastic carry case