



18 V + 18 V → **36 V**



## KHA 36-18 LTX 32 with Metabo Quick change chuck

- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- 100% compatibility with the 18 Volt class: powerful 36 Volt operation with two 18 Volt battery packs from Metabo
- Metabo VibraTech (MVT): working, also continuously, in a low-fatigue manner whilst protecting the user's health
- Ergonomic housing shape for chiselling tasks without side handle
- Metabo Quick: fast, tool-free chuck for working with SDS-plus and straight shank drill bits
- Variospeed (V) Electronics for working at customised speeds to suit various application materials
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	600796840
EAN code	4007430318053
Type of battery pack	Li-Power
Battery voltage	18 V
Max. single blow energy (EP-TA)	3.1 J
Maximum impact rate	4500 bpm
Drill-Ø concrete with hammer drills	32 mm / 1 1/4 "
Drill-Ø masonry with core bits	68 mm / 2 11/16 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1100 rpm
Bit retainer	SDS-plus
Weight without battery pack	3.8 kg / 8.4 lbs
Weight with battery pack	5.1 kg / 11.2 lbs

### Scope of delivery

Hammer chuck for tools with SDS-plus shank end, Keyless chuck for tools with cylindrical shank, Metabo VibraTech (MVT) side handle, Drilling depth guide, metaBOX 165 L, without battery pack, without charger