



P 6000 Inox

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Metabo pump protection: automatic dry-run protection with LED display to protect the pump and high user safety
- Multi-level pump running gear for high performance and low-noise operation
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Durable stainless steel pump housing
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- Ergonomic handle for comfortable transport
- For garden irrigation with 1 to 4 sprinklers

Order no.	600966000
EAN code	4007430240538
Rated input power	1300 W
Maximum delivery rate	6000 l/h / 1585 gal/h
Maximum delivery height	55 m / 180 ft
Maximum pressure	5.5 bar / 79.8 psi
Maximum suction height	8 m / 26 ft
Suction port	1" female thread
Discharge port	1" female thread
Pump housing	Stainless steel
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	5
Dimensions	470 x 222 x 303 mm // 18 1/2 x 8 3/4 x 11 15/16 "
Weight	12.7 kg / 28 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Fabric Sealing Tape