



P 2000 G

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- Ergonomic handle for comfortable transport
- For garden irrigation with 1 or 2 sprinklers

Order no.	600962000
EAN code	4007430240750
Rated input power	450 W
Maximum delivery rate	2000 l/h / 528 gal/h
Maximum delivery height	30 m / 98 ft
Maximum pressure	3 bar / 43.5 psi
Maximum suction height	8 m / 26 ft
Suction port	1" female thread
Discharge port	1" female thread
Pump housing	Grey cast iron
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	1
Dimensions	350 x 190 x 260 mm // 13 25/32 x 7 1/2 x 10 1/4 "
Weight	7.6 kg / 16.8 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Fabric Sealing Tape