



P 9000 G

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- For garden irrigation with 1 to 6 sprinklers

Order no.	600967000
EAN code	4007430240521
Rated input power	1900 W
Maximum delivery rate	9000 l/h / 2378 gal/h
Maximum delivery height	51 m / 167 ft
Maximum pressure	5.1 bar / 74 psi
Maximum suction height	9 m / 30 ft
Suction port	1 1/4" female thread
Discharge port	1" female thread
Pump housing	Grey cast iron
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	1
Dimensions	517 x 206 x 237 mm // 20 11/32 x 8 1/8 x 9 5/16 "
Weight	25.1 kg / 55.3 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Fabric Sealing Tape