



P 3300 G

- For garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- Ergonomic handle for comfortable transport
- For garden irrigation with 1 or 2 sprinklers

| Order no. | 600963000 |
|-------------------------|---|
| EAN code | 4007430240590 |
| Rated input power | 900 W |
| Maximum delivery rate | 3300 l/h / 872 gal/h |
| Maximum delivery height | 45 m / 148 ft |
| Maximum pressure | 4.5 bar / 65.3 psi |
| Maximum suction height | 8 m / 26 ft |
| Suction port | 1" female thread |
| Discharge port | 1" female thread |
| Pump housing | Grey cast iron |
| Protection type IP | IP X4 |
| Drive shaft | Stainless steel |
| Number of impellers | 1 |
| Dimensions | 380 x 210 x 290 mm // 14 31/32 x 8 1/4 x 11 13/32 " |
| Weight | 11.1 kg / 24.5 lbs |
| Cable length | 1.5 m / 5 ft |

Scope of delivery

Fabric Sealing Tape