



## HWW 4500/25 Inox

- For automatic water supply, for garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Pressure vessel for energy-saving and low-noise provision of water
- Pressure switch at the tank for automatic activation in case of increased water demand
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Durable stainless steel pump housing
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- For garden irrigation with 1 to 3 sprinklers
- For single phase alternating current

Order no.	600972000
EAN code	4007430239501
Rated input power	1300 W
Maximum delivery rate	4500 l/h / 1189 gal/h
Maximum delivery height	48 m / 157 ft
Maximum pressure	4.8 bar / 70 psi
Maximum suction height	8 m / 26 ft
Switch-on pressure approx.	1.8 bar / 26.1 psi
Switch-off pressure approx.	3.6 bar / 52.2 psi
Suction port	1" female thread
Discharge port	1" female thread
Tank capacity, approximately	24 l / 6.3 gal
Pump housing	Stainless steel
Protection type IP	IP X4
Drive shaft	Stainless steel
Tank	Steel
Number of impellers	1
Dimensions	484 x 307 x 600 mm // 19 1/16 x 12 3/32 x 23 5/8 "
Weight	17.1 kg / 37.7 lbs
Cable length	1.5 m / 5 ft

### Scope of delivery

Check Valve, Fabric Sealing Tape