



HWW 6000/50 Inox

- For automatic water supply, for garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Pressure vessel for energy-saving and low-noise provision of water
- Electronic pressure switch at the boiler for automatic activation in case of increased water demand
- Metabo pump protection: automatic dry-run protection with LED display to protect the pump and high user safety
- Multi-level pump running gear for high performance and low-noise operation
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Durable stainless steel pump housing
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- For garden irrigation with 1 to 4 sprinklers
- For single phase alternating current

Order no.	600976000
EAN code	4007430239464
Rated input power	1300 W
Maximum delivery rate	6000 l/h / 1585 gal/h
Maximum delivery height	55 m / 180 ft
Maximum pressure	5.5 bar / 79.8 psi
Maximum suction height	8 m / 26 ft
Switch-on pressure approx.	1.6 bar / 23.2 psi
Switch-off pressure approx.	5.5 bar / 79.8 psi
Suction port	1" female thread
Discharge port	1" female thread
Tank capacity, approximately	50 l / 13.2 gal
Pump housing	Stainless steel
Protection type IP	IP X4
Drive shaft	Stainless steel
Tank	Steel
Number of impellers	5
Dimensions	645 x 395 x 715 mm // 25 3/8 x 15 9/16 x 28 5/32 "
Weight	22.1 kg / 48.7 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Check Valve, Fabric Sealing Tape