



HWW 9000/100 G

- For automatic water supply, for garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Pressure vessel for energy-saving and low-noise provision of water
- Pressure switch at the tank for automatic activation in case of increased water demand
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- For garden irrigation with 1 to 6 sprinklers
- For single phase alternating current

Order no.	600977000
EAN code	4007430239280
Rated input power	1900 W
Maximum delivery rate	9000 l/h / 2378 gal/h
Maximum delivery height	51 m / 167 ft
Maximum pressure	5.1 bar / 74 psi
Maximum suction height	9 m / 30 ft
Switch-on pressure approx.	1.5 bar / 21.8 psi
Switch-off pressure approx.	3.9 bar / 56.6 psi
Suction port	1 1/4" female thread
Discharge port	1" female thread
Tank capacity, approximately	100 l / 26.4 gal
Pump housing	Grey cast iron
Protection type IP	IP X4
Drive shaft	Stainless steel
Tank	Steel
Number of impellers	1
Dimensions	730 x 448 x 740 mm // 28 3/4 x 17 5/8 x 29 1/8 "
Weight	39.9 kg / 83.6 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Check Valve, Fabric Sealing Tape