



## HWA 3500 Inox

- For automatic water supply, for garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Intelligent electronics for automatic appropriate and energy-saving modes
- Metabo pump protection: automatic dry-run protection with LED display to protect the pump and high user safety
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Durable stainless steel pump housing
- Separate water filling opening for comfortable operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- Rubberised feet for low-noise and low-vibration operation
- For garden irrigation with 1 or 2 sprinklers

Order no.	600978000
EAN code	4007430240514
Rated input power	1100 W
Maximum delivery rate	3500 l/h / 925 gal/h
Maximum delivery height	45 m / 148 ft
Maximum pressure	4.5 bar / 65.3 psi
Maximum suction height	8 m / 26 ft
Switch-on pressure approx.	1.6 bar / 23.2 psi
Switch-off pressure approx.	4.5 bar / 65.3 psi
Suction port	1" female thread
Discharge port	1" female thread
Pump housing	Stainless steel
Protection type IP	IP X4
Drive shaft	Stainless steel
Number of impellers	1
Dimensions	408 x 222 x 303 mm // 16 1/16 x 8 3/4 x 11 15/16 "
Weight	10.6 kg / 23.4 lbs
Cable length	1.5 m / 5 ft

### Scope of delivery

Check Valve, Fabric Sealing Tape