



HWW 3500/25 G

- For automatic water supply, for garden irrigation and groundwater pumping as well as pumping, pumping empty, circulation of clear water
- Pressure vessel for energy-saving and low-noise provision of water
- Pressure switch at the pump head for automatic activation in case of increased water demand
- Maintenance-free capacitor motor
- Overload protection: protects the motor from overheating
- High-quality slip seal system for long service life
- Separate water filling opening for simple operation of the pump
- Water drain plug (removable without tools) for protection in case of frost
- For garden irrigation with 1 or 2 sprinklers
- For single phase alternating current

Order no.	600981000
EAN code	4061792001541
Rated input power	900 W
Maximum delivery rate	3500 l/h / 925 gal/h
Maximum delivery height	45 m / 147 ft
Maximum pressure	4.5 bar / 65 psi
Maximum suction height	8 m / 26 ft
Switch-on pressure approx.	1.4 bar / 20.3 psi
Switch-off pressure approx.	3.2 bar / 46.4 psi
Suction port	1" female thread
Discharge port	1" female thread
Tank capacity, approximately	24 l / 6.3 gal
Pump housing	Grey cast iron
Protection type IP	IP X4
Drive shaft	Stainless steel
Tank	Steel
Number of impellers	1
Dimensions	470 x 270 x 575 mm // 18 1/2 x 10 5/8 x 22 5/8 "
Weight	15.9 kg / 35.1 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Check Valve, Fabric Sealing Tape