



## HG 16-500

- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

<b>Order no.</b>	<b>601067500</b>
<b>EAN code</b>	<b>4061792185937</b>
Air volume	240 / 450 l/min // 8 / 16 cfm
Air temperature	300 / 500 °C // 570 / 930 °F
Number of air temperature levels	2
Input power max.	1600 W
Weight (without power cable)	0.6 kg / 20.8 oz
Cable length	2.2 m / 7 ft

### Scope of delivery

Wide jet nozzle (50 mm), Wrap around nozzle, meta-BOX 145