



WEV 17-125 Quick RT with speed control, quick-locking nut

- Maximum productivity thanks to top performance with low weight; with speed control
- Perfect ergonomics thanks to slim handle for maximum control and easy working overhead
- Metabo Marathon-motor with new cooling and carbon brush system for twice the service life
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- M-Quick System for tool-free disc change at the touch of a button
- Tool-free adjustable guard; twist-proof
- Low-vibration side handle Metabo VibraTech (MVT)
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Electronic soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Order no.	601089000
EAN code	4007430314161
Disc-Ø	125 mm // 5 "
Rated input power	1750 W
Output power	1070 W
No-load speed	2800 - 11000 rpm
Speed at rated load	11000 rpm
Torque	3.8 Nm / 34 in-lbs
Spindle thread	M 14
Handle circumference	138 mm / 5.438 "
Weight (without power cable)	2.5 kg / 5.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Metabo VibraTech (MVT) side handle