



WEV 1500-125 Quick RT with speed control, quick-locking nut

- Efficient and robust angle grinder with ergonomic soft handle for low-fatigue working, especially overhead
- Powerful and robust angle grinder with speed control and ergonomic soft handle for low-fatigue working, especially overhead
- Powerful motor with good overload capacity
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Electronic soft start for smooth start-up
- Restart protection after power interruption
- Auto-stop carbon brushes to protect the motor

Order no.	601243500
EAN code	4007430297402
Disc-Ø	125 mm // 5 "
Rated input power	1500 W
Output power	900 W
No-load speed	3500 - 11000 rpm
Speed at rated load	11000 rpm
Torque	4.2 Nm / 37.2 ft. lbs
Spindle thread	M 14
Handle circumference	138 mm / 5.438 "
Weight (without power cable)	2.4 kg / 5.3 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, "Quick" flange nut, Side handle, Plastic carry case