



Basic 250-50 W

- Powerful, robust compressor for simple, commercial use
- Oil-lubricated Piston Condenser
- For single phase alternating current
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels for mobile use
- Additional manometer for displaying the tank pressure
- Rubber-coated handle for comfortable handling
- 10 year tank warranty against rust

Order no.	601534000
EAN code	4007430244437
Suction rate	200 l/min / 7.1 cfm
Filling capacity	110 l/min / 3.9 cfm
Effective delivery volume (at 80% max. pressure)	95 l/min / 3.4 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	1.5 kW / 2 HP
Maximum speed	2850 rpm
Tank capacity	50 l / 13.2 gal
Sound pressure level (LpA)	81 dB(A)
Sound power level (LwA)	97 dB(A)
Dimensions	780 x 400 x 625 mm // 30 23/32 x 15 3/4 x 24 5/8 "
Weight	32 kg / 70.5 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

Universal quick-action coupling, Pull handle with rubber-grip