



Mega 400-50 D

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Oil-lubricated Piston Condenser
- For three-phase current
- Working pressure can be regulated according to application and air quality improved thanks to the filter pressure reducer with manometer and oil-mist lubricator
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Instrument panel with easy to read manometer for tank- and working pressure
- Large, rubberised wheels for comfortable transport
- Steering castors with locking brake for high manoeuvrability
- Cable winding mechanism
- Ergonomic and long pull handle with integrated cable drum
- 10 year tank warranty against rust

Order no.	601537000
EAN code	4007430244468
Suction rate	400 l/min / 106 gal/h
Filling capacity	300 l/min / 10.6 cfm
Effective delivery volume (at 80% max. pressure)	260 l/min / 9.2 cfm
Maximum pressure	10 bar / 145 psi
Mains voltage	380 - 415 V
Rated input power	2.2 kW / 3 HP
Maximum speed	1050 rpm
Tank capacity	50 l / 13.2 gal
Sound pressure level (LpA)	86 dB(A)
Sound power level (LwA)	93 dB(A)
Dimensions	1050 x 410 x 817 mm // 3.4 x 1.4 x 2.7 ft
Weight	73 kg / 161 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

3 Universal couplings