



## Basic 280-50 W OF

- Powerful, robust compressor for simple, commercial use
- Oil-free piston compressor: simple transportation and reduced service requirements
- For single phase alternating current
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels for mobile use
- No testing required before initial operation
- Additional manometer for displaying the tank pressure
- Rubber-coated handle for comfortable handling
- 10 year tank warranty against rust

Order no.	601529000
EAN code	4007430322203
Suction rate	280 l/min / 9.9 cfm
Filling capacity	140 l/min / 4.9 cfm
Effective delivery volume (at 80% max. pressure)	130 l/min / 4.6 cfm
Maximum pressure	8 bar / 116 psi
Rated input power	1.7 kW / 2.5 HP
Maximum speed	2850 rpm
Tank capacity	50 l / 13.2 gal
Sound pressure level (LpA)	85 dB(A)
Sound power level (LwA)	97 dB(A)
Dimensions	770 x 386 x 662 mm // 30 5/16 x 15 3/16 x 26 1/16 "
Weight	30 kg / 66.1 lbs
Cable length	1.5 m / 5 ft

### Scope of delivery

Universal quick-action coupling, Pull handle with rubber-grip