



Mega 350-100 D

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Oil-lubricated Piston Condenser
- For three-phase current
- Working pressure can be regulated according to application by means of a filter pressure reducer with manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels and pull handle for mobile use
- 10 year tank warranty against rust

Order no.	601539000
EAN code	4007430244765
Suction rate	320 l/min / 85 gal/h
Filling capacity	250 l/min / 8.8 cfm
Effective delivery volume (at 80% max. pressure)	220 l/min / 7.8 cfm
Maximum pressure	10 bar / 145 psi
Mains voltage	380 - 415 V
Rated input power	2.2 kW / 3 HP
Maximum speed	1350 rpm
Tank capacity	90 l / 23.8 gal
Sound pressure level (LpA)	86 dB(A)
Sound power level (LwA)	93 dB(A)
Dimensions	1000 x 410 x 900 mm // 3.3 x 1.4 x 3 ft
Weight	69 kg / 152 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

3 Universal couplings