



Mega 400-50 W

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Oil-lubricated Piston Condenser
- For single phase alternating current
- Working pressure can be regulated according to application and air quality improved thanks to the filter pressure reducer with manometer and oil-mist lubricator
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Instrument panel with easy to read manometer for tank- and working pressure
- Large, rubberised wheels for comfortable transport
- Steering castors with locking brake for high manoeuvrability
- Cable winding mechanism
- Ergonomic and long pull handle with integrated cable drum
- 10 year tank warranty against rust

| Order no. | 601536000 |
|--|---|
| EAN code | 4007430244451 |
| Suction rate | 400 l/min / 106 gal/h |
| Filling capacity | 300 l/min / 10.6 cfm |
| Effective delivery volume (at 80% max. pressure) | 260 l/min / 9.2 cfm |
| Maximum pressure | 10 bar / 145 psi |
| Mains voltage | 220 - 240 V |
| Rated input power | 2.2 kW / 3 HP |
| Maximum speed | 1050 rpm |
| Tank capacity | 50 l / 13.2 gal |
| Sound pressure level (LpA) | 86 dB(A) |
| Sound power level (LwA) | 93 dB(A) |
| Dimensions | 1050 x 410 x 817 mm // 3.4 x 1.4 x 2.7 ft |
| Weight | 73 kg / 161 lbs |
| Cable length | 1.5 m / 5 ft |

Scope of delivery

3 Universal couplings