



Power 250-10 W OF

- Compact and mobile piston compressor for flexible use both indoors and on construction sites
- Portable assembly compressor – ideal for tackers and nails as well as for splitting pipes
- For single phase alternating current
- Oil-free piston compressor: simple transportation and reduced service requirements
- Instrument panel with easy to read manometer for tank- and working pressure
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Fittings and control elements protected in tubular frames and clearly visible
- Cable winding mechanism
- Convenient pressure switch for good cold starting, complete with relief valve
- Overload protection: protects the motor from overheating
- Rubberised feet for optimum stability
- Crane eyelet for safe and easy transport on the construction site

Order no.	601544000
EAN code	4007430244857
Suction rate	220 l/min / 58 gal/h
Filling capacity	120 l/min / 4.2 cfm
Effective delivery volume (at 80% max. pressure)	100 l/min / 3.5 cfm
Maximum pressure	10 bar / 145 psi
Rated input power	1.5 kW / 2 HP
Maximum speed	2850 rpm
Tank capacity	10 l / 2.6 gal
Sound pressure level (LpA)	84 dB(A)
Sound power level (LwA)	97 dB(A)
Dimensions	470 x 480 x 348 mm // 1.6 x 1.6 x 1.1 ft
Weight	24 kg / 52.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

2 Universal quick-action couplings