



Power 280-20 W OF

- Compact and mobile piston compressor for flexible use both indoors and on construction sites
- For single phase alternating current
- Oil-free piston compressor: simple transportation and reduced service requirements
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Fittings and control elements protected in tubular frames and clearly visible
- Rubberised, stable wheels and pull handle for mobile use
- Cable winding mechanism
- Convenient pressure switch for good cold starting, complete with relief valve
- Overload protection: protects the motor from overheating
- Rubberised feet for optimum stability
- Attachment and transport option for Metaloc and other common storage case systems
- Crane eyelet for safe and easy transport on the construction site

Order no.	601545000
EAN code	4007430244864
Suction rate	280 l/min / 74 gal/h
Filling capacity	150 l/min / 5.3 cfm
Effective delivery volume (at 80% max. pressure)	140 l/min / 5 cfm
Maximum pressure	10 bar / 145 psi
Rated input power	1.7 kW / 2.5 HP
Maximum speed	2850 rpm
Tank capacity	20 l / 5.3 gal
Sound pressure level (LpA)	83 dB(A)
Sound power level (LwA)	97 dB(A)
Dimensions	580 x 600 x 500 mm // 1.9 x 2 x 1.7 ft
Weight	40 kg / 88.2 lbs
Cable length	4 m / 13 ft

Scope of delivery

2 Universal quick-action couplings