



Mega 700-90 D

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Two-stage compression for particularly high performance and long service life
- For three-phase current
- Working pressure can be regulated according to application and air quality improved thanks to the filter pressure reducer with manometer and oil-mist lubricator
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Oil-lubricated 2-cylinder piston compressors for high air supply volume
- Instrument panel with easy to read manometer for tank- and working pressure
- Re-cooler for less condensation water formation
- Large, rubberised wheels for comfortable transport
- Steering castors with locking brake for high manoeuvrability
- Cable winding mechanism
- Ergonomic and long pull handle with integrated cable drum
- 10 year tank warranty against rust

Order no.	601542000
EAN code	4007430244833
Suction rate	650 l/min / 172 gal/h
Filling capacity	520 l/min / 18.4 cfm
Effective delivery volume (at 80% max. pressure)	450 l/min / 15.9 cfm
Maximum pressure	11 bar / 160 psi
Mains voltage	380 - 415 V
Rated input power	4 kW / 5.5 HP
Maximum speed	1400 rpm
Tank capacity	90 l / 23.8 gal
Sound pressure level (LpA)	88 dB(A)
Sound power level (LwA)	97 dB(A)
Dimensions	1188 x 520 x 1110 mm // 3.9 x 1.7 x 3.7 ft
Weight	119 kg / 262 lbs
Cable length	1.5 m / 5 ft

Scope of delivery

3 Universal couplings