



## DKS 10 Set

- Suitable for cutting metal sheets, plastics, aluminium, wood and fibre glass
- Low vibrations for convenient continuous mode
- Magnesium housing: particularly light and robust
- Rubberised handle for ergonomic and fatigue-free operation
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Sound-proofed air outlet for reduced noise operation
- Precise saw blade guide for high cutting output and clean cutting edges
- Adjustable hoop guard: exact setting of cutting depth
- Safety lever prevents unintentional start of the machine

Order no.	601560500
EAN code	4007430245830
Operating pressure	6.2 bar / 90 psi
Air requirement	420 l/min / 15 cfm
Cutting thickness aluminum	4 mm / 5/32 "
Cutting thickness steel	3 mm / 1/8 "
Stroke length	10 mm / 3/8 "
Strokes at rated load	9000 spm
Weight	0.65 kg / 1.4 lbs

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", 5 Saw blades each (18 teeth, 24 teeth, 32 teeth), Hexagonal wrench, Plastic carry case, Hose nozzle 10 mm and hose clamp according to ISO 11148, Oil bottles