



DMH 290 Set

- Light, handy chipping hammer
- For processing of sheet metal and stone
- For work in the car body area
- Suitable for construction work on masonry, bricks, aerated concrete
- Ideal for removing plaster and tiles and light mortising work
- Kickback damping for reduction of vibrations
- Long piston stop with higher power transmission, effective operation and rapid work progress
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Quick-action chuck: for quick and tool-free change of chisels
- Rubberised handle for ergonomic and fatigue-free operation

Order no.	601561500
EAN code	4007430245878
Operating pressure	6.2 bar // 90 psi
Air requirement	330 l/min / 12 cfm
Bit retainer	Hexagon shaft 10 mm
Impact rate	2900 bpm
Weight	1.7 kg / 3.7 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Hose nozzle 10 mm and hose clamp according to ISO 11148, 3 Chisels, Quick-change Chuck, Plastic carry case, Oil bottles