



RM 36-18 LTX BL 46

- Quiet cordless lawn mower for efficient mowing, collecting and mulch of plots of land up to 800 m²
- Mowed material is optionally ejected at the back, collected in the flexible collection bag or mulched immediately
- Powerful brushless motor for high cutting performance and long runtime per battery pack charge
- Automatic adaptation of the motor performance depending on the grass height for maximum battery pack runtimes
- Central, easy-to-operate cutting height setting in 7 stages
- Easy steering and tracking by means of smooth running wheels and height-adjustable push handle with rubberised grip area
- Robust and durable thanks to metal cover and high-quality mower blade
- Double protection from unintentional startup thanks to safety key and safety switch
- Easy transport and space-saving storage thanks to carry handles and double folding bow handle
- Well-visible capacity display for checking the battery pack charge status
- Environmentally-friendly and quiet thanks to battery operations, therefore usable also in areas sensitive to noise
- 100% compatibility with the 18 Volt class: powerful 36 Volt operation with two 18 Volt battery packs from Metabo
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

| Order no. | 601606850 |
|-----------------------------|----------------------------|
| EAN code | 4061792176690 |
| Battery voltage | 18 V |
| Cutting width | 46 cm / 18 " |
| Cutting height | 25 - 80 mm // 1 - 3 5/32 " |
| Cutting height stages | 7 |
| Collection bag volume | 55 l |
| No-load speed | 2800 rpm |
| Maximum speed | 3400 rpm |
| Weight without battery pack | 24.5 kg / 54 lbs |
| Weight with battery pack | 25.4 kg / 56 lbs |

Scope of delivery

Collection bag, Mower blade, Mulching key, Safety key, without battery pack, without charger