



## Mega 580-200 D

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Two-stage compression for particularly high performance and long service life
- For three-phase current
- Working pressure can be regulated according to application by means of a filter pressure reducer with manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Oil-lubricated 2-cylinder piston compressors for high air supply volume
- Rubberised, stable wheels and pull handle for mobile use
- 10 year tank warranty against rust

Order no.	601588000
EAN code	4007430253866
Suction rate	510 l/min / 135 gal/h
Filling capacity	395 l/min / 14 cfm
Effective delivery volume (at 80% max. pressure)	360 l/min / 12.7 cfm
Maximum pressure	11 bar / 160 psi
Mains voltage	380 - 415 V
Rated input power	3 kW / 4 HP
Maximum speed	1400 rpm
Tank capacity	200 l / 52.8 gal
Sound pressure level (LpA)	87 dB(A)
Sound power level (LwA)	96 dB(A)
Dimensions	1430 x 550 x 1010 mm // 4.7 x 1.8 x 3.3 ft
Weight	136 kg / 300 lbs
Cable length	1.5 m / 5 ft

### Scope of delivery

3 Universal couplings