



## DW 10-125 Quick

- Particularly powerful and robust for demanding use
- For grinding flat and curved surfaces in a variety of different materials
- Ergonomic, insulated and lightweight housing made from impact-proof plastic
- Metabo VibraTech (MVT) side handle for vibration damping to protect the user's health
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; rotatable and fixable in 8 positions
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Sound-proofed air outlet for reduced noise operation
- Safety lever prevents unintentional start of the machine
- For use with roughing and separating discs Ø 125 mm
- Numerous grinding wheels and cutting discs are available in the Metabo range

<b>Order no.</b>	<b>601591000</b>
<b>EAN code</b>	<b>4007430335371</b>
Disc-Ø	125 mm / 5 "
Operating pressure	6.2 bar / 90 psi
Air requirement	500 l/min / 18 cfi
No-load speed	12000 rpm
Spindle thread	M 14
Weight	2 kg / 4.4 lbs

### Scope of delivery

EURO Plug-in nipple 3/8", ARO/Orion Plug-in nipple 3/8", ISO Plug-in nipple 3/8", Hexagonal wrench, Anti-vibration handle, Protective cover for disc, Oil bottles