



KH 18 LTX BL 24

- Very lightweight, compact cordless hammer with brushless motor for low-fatigue drilling in any working position
- Maximum drill performance, efficiency and service life thanks to brushless technology and high-performance hammer action
- Dust-free drilling with external dust extraction ESA plus
- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo VibraTech (MVT): working, also continuously, in a low-fatigue manner whilst protecting the user's health
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Electronic soft start for precise spot-drilling
- Safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601713840
EAN code	4061792218505
Battery voltage	18 V
Max. single blow energy (EP-TA)	2.2 J
Maximum impact rate	4750 bpm
Drill-Ø concrete with hammer drills	24 mm / 1 "
Drill-Ø masonry with core bits	82 mm / 3 7/32 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1280 rpm
Bit retainer	SDS-plus
Weight without battery pack	2.7 kg / 5.95 lbs

Scope of delivery

rubber-coated side handle, Drilling depth guide, metaBOX 165 L, without battery pack, without charger