



SCV 18 LTX BL 1.6

- Very handy and manoeuvrable cordless metal shears for burr-free cutting of sheet metal on site
- Maximum cornering ability, for comfortable cutting of narrow radii from 15 mm
- Faster working, thanks to the efficient brushless motor
- Infinitely adjustable cutting speed for individual customisation to the given material and task at hand
- Comfortable handling thanks to low weight, slim grip area and switch located on the top
- Blade spacing can be flexibly adjusted to different sheet thicknesses
- Economical four-way reversible blade, with the highest cut quality
- Maximum safety in every cutting direction, thanks to large hand guard
- Electronic overload protection for long service life
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601615840
EAN code	4061792183339
Type of battery pack	Li-Power
Battery voltage	18 V
Max. sheet thickness for steel: 400 N/mm ²	1.6 mm / 0.0629 "
Max. sheet thickness for steel: 600 N/mm ²	1.2 mm / 0.0472 "
Max. sheet thickness for steel: 800 N/mm ²	0.7 mm / 0.0275 "
Max. sheet thickness for aluminium: 250 N/mm ²	2 mm / 0.0787 "
Strokes in idle	1350 - 4840 rpm
Cutting speed	7 m/min // 275 inch/min
Starting hole diameter	27 mm / 1.0629 "
Smallest curve radius	15 mm / 0.5905 "
Weight without battery pack	1.4 kg / 3.1 lbs
Weight with battery pack	1.8 kg / 4 lbs

Scope of delivery

2 reversible blades, Feeler gauge, 2 Hexagonal wrenches, metaBOX 145, without battery pack, without charger