



HS 18 LTX BL 65

- Powerful, Brushless cordless hedge trimmer with rotating handle for comfortable trimming and pruning applications
- Powerful Brushless motor for maximum cutting output and long battery pack runtime
- Highly efficient, precise dual cutting system thanks to diamond-ground blade teeth on both sides
- Rotating handle with 5 positions for safe and flexible guiding the hedge trimmer
- Comfortable two-hand operation thanks to long trigger button with inside bow-type handle switch
- Safe working thanks to perfect balance, softgrip handle, hand protection at the blade and quick stop (in 0.2 seconds)
- Metabo VibraTech (MVT): integrated vibration damping for healthy working also in continuous mode
- Central control panel: ON/OFF safety switch with standby function and LED control displays
- Metabo S-automatic safety clutch: Protects blades and gears when debris or large branches stop the blades
- Robust use thanks to magnesium gear housing and protected position of the battery pack
- Trigger guard protects user and gearing when working near walls and the ground
- Space-saving storage at the wall by means of practical suspension eye
- Environmentally-friendly and quiet thanks to battery operations, therefore usable also in areas sensitive to noise
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601723850
EAN code	4061792228443
Battery voltage	18 V
Blade length	65 cm / 26 "
Cutting length	60 cm / 23 "
Max. cutting thickness	21 mm / 13/16 "
Number of strokes (No Load)	3400 spm
Weight without battery pack	4.2 kg / 9.3 lbs
Weight with battery pack	4.6 kg / 10.1 lbs

Scope of delivery

Blade protection quiver, without battery pack, without charger