



MA-MS 25

- Safe tree maintenance with the pole pruner attachment of the Metabo multifunction system, the all-in-one solution for many garden applications
- Together with the cordless multifunction drive MA 36-18 LTX BL Q an environmentally-friendly, quiet system, ideal for areas sensitive to noise
- Metabo "Quick" quick coupling system for tool-free attachment replacement
- Precise and powerful cuts with a chain speed of up to 18 m/s
- Shaft extension to increase the range by 88 cm available as accessory
- Low kickback chain for easy, safe cuts and low vibrations
- Automatic chain lubrication for highest cutting output with minimum service requirements
- Easy re-tensioning and replacement of the saw chain
- Stable stop made from metal for optimal guidance and low-fatigue sawing
- Integrated hook for the removal of cut branches from the tree-top
- Semi-transparent oil tank for comfortable controlling and refilling of the chain oil
- Robust use thanks to durable metal gear unit

Order no.	601727850
EAN code	4061792229518
Track length	25 cm / 9 27/32 "
Cutting length	24 cm / 9 7/16 "
Max. chain speed level 1	16 m/s / 53 ft/s
Max. chain speed level 2	18 m/s / 59 ft/min
Saw chain tooth shape	semi-chisel / low profile
Saw chain tooth division	3/8" LP
Drive link thickness	1.3 mm / 0.05 "
Number of drive links	39
Oil container volume	120 ml
Length	1230 mm / 48 7/16 "
Length with drive	2005 mm / 78 15/16 "
Weight	1.7 kg / 3.7 lbs

Scope of delivery

Saw chain 25 cm (3/8" LP / 1.3 mm), Saw rail 25 cm, Sawing chain protection, Combo-spanner