



FM 500-6

- Light, compact bevelling tool for single-handed profile cutting, trimming and cutting of grooves
- Powerful motor for quick cutting of wood and wood-like materials
- With extensive scope of delivery: parallel guide, template follower and roller guide
- Precise, stepless depth adjustment and fixing of the motor unit using rack jacks
- Transparent baseplate for maximum view of the router bit and workpiece
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor

Order no.	601741000
EAN code	4061792243064

Maximum stroke height	40 mm / 1.56 "
No-load speed	32000 rpm
Rated input power	500 W
Output power	300 W
Speed at rated load	19000 rpm
Collet chuck bore	6 mm / 1/4 "
Weight (without power cable)	1.3 kg / 2.9 lbs
Cable length	2 m / 78 3/4 "

Scope of delivery

2 open-jawed spanners, Parallel guide, Template Follower, Roller guide, Protective glass