



KFM 18 LTX 3 RF

- The most powerful cordless metal beveling tool for 45° chamfers up to 4 mm and radii of 2 and 3 mm
- Surfaces free from oxide and burrs as ideal preparation for the application of powder or paint coatings for maximum protection from corrosion
- One-touch controller: Patented, tool-free setting of the cutting depth in 0.1 steps; stop points for short setting times, and protection against unintentional adjustment of the cutting depth when working
- Slim milling head and ball bearing stationary seal ring for working in pipes and on curves
- Guide stop for a uniform finish and high quality of the surface when processing straight sheets
- Bail handle adjusts without tools for secure, even guiding
- Battery pack can be swivelled for better access in hard to reach places
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after battery pack change
- Detachable dust protection filter protects motor from coarse particles
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601754840
EAN code	4007430291462

Type of battery pack	Li-Power
Battery voltage	18 V
No-load speed	7000 rpm
Type of edges	Chamfer and radius
Max. chamfer width 45°	6 mm / 1/4 "
Max. chamfer height at 45°	4 mm / 5/32 "
Possible radii	R2 / R3
Grading of cutting depth setting	0.1 mm / 0.00394 "
Curves smallest internal Ø	13 mm
Weight without battery pack	2.4 kg / 5.3 lbs
Weight with battery pack	3.1 kg / 6.8 lbs

Scope of delivery

2 Carbide indexable inserts 45° chamfer, 2 Carbide indexable inserts radius R2, 2 Carbide indexable inserts radius R3, Guide Stop, Screwdriver for Torx screws 15, Bow-type handle, Dust protection filter, metaBOX 215, without battery pack, without charger