



KFM 9-3 RF

- Compact metal beveling tool for 45° chamfers and radii of 2 to 3 mm at visible edges
- Surfaces free from oxide and burrs as ideal preparation for the application of powder or paint coatings for maximum protection from corrosion
- One-touch controller: Patented, tool-free setting of the cutting depth in 0.1 steps; stop points for short setting times, and protection against unintentional adjustment of the cutting depth when working
- Slim cutter head with standard carbide indexable inserts and ball-bearing stationary seal ring for working in tubes and in curves
- Guide stop for a uniform finish and high quality surface finish when processing straight edges
- Bail handle adjusts without tools for secure, even guiding
- Metabo Marathon-motor with patented dust protection for long service life
- Thumbwheel controlled Vario-Constamatic (VC)-Full wave electronics ideal for working on materials requiring customised speeds, and at speeds which remain almost constant under load
- Electronic safety shutdown of the motor for safe working in case the tool stops unexpectedly
- Electronic overload protection, soft start and restart protection
- Slim design for ideal handling
- With metaBOX, the intelligent solution for transport and storage

Order no.	601751700
EAN code	4007430293404
No-load speed	4500 - 11500 rpm
Rated input power	900 W
Output power	470 W
Type of edges	Chamfer and radius
Max. chamfer width 45°	6 mm / 1/4 "
Max. chamfer height at 45°	4 mm / 5/32 "
Possible radii	R2 / R3
Grading of cutting depth setting	0.1 mm / 0.00394 "
Curves smallest internal Ø	13 mm
Weight (without power cable)	2.5 kg / 5.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

2 carbide indexable inserts 45° chamfer (ISO: DCMT 11 T 304), 2 Carbide indexable inserts radius R2, 2 Carbide indexable inserts radius R3, Guide Stop, Screwdriver for Torx screws 15, Bow-type handle, metaBOX 215