



## CS 22-355

- Powerful metal chop saw for cutting of profiles, pipes and rods made of steel, NF metals, iron and cast profiles
- Quick clamping device with variable mitre setting for angled cuts from -15° to 45°
- Large handle transversal to the cutting axis for optimum power transmission while cutting
- Adjustable cutting depth limiter for optimum use of the cutting disc
- Easy, fast disc change with spindle lock
- Maximum user safety: swivelling cutting guard, adjustable spark deflector sheet and rubberised base for safe cutting
- Safety switch for protection against accidental start up
- Robust, large machine table with practical storage for hexagonal wrenches
- Easy to transport due to built-in handle and locking device

| Order no.                              | 60178600                             |
|--|--------------------------------------|
| EAN code                               | 4061792211773                        |
| Grinding wheels (Ø x bore)             | 355 x 25.4 mm // 13 31/32 x 1 "      |
| No-load speed                          | 3700 rpm                             |
| Rated input power                      | 2300 W                               |
| Max. cutting capacity round tube       | 132 mm / 5 3/16 "                    |
| Max. cutting capacity square tube      | 120 x 120 mm // 4 23/32 x 4 23/32 "  |
| Max. cutting capacity rectangular tube | 100 x 208 mm // 3 15/16 x 8 3/16 "   |
| Max. cutting capacity L-profile        | 150 x 150 mm // 5 29/32 x 5 29/32 "  |
| Dimensions of the base plate           | 456 x 256 mm // 17 15/16 x 10 1/16 " |
| Transport height                       | 394 mm / 15 1/2 "                    |
| Weight                                 | 16.8 kg / 37 lbs                     |
| Cable length                           | 4 m / 13 ft                          |

### Scope of delivery

Hexagonal wrench, Inner support flange, Flange nut, Cutting disc 355 mm