



## KFMPB 15-10 F

- Metal bevelling tool for chamfer heights up to 10 mm for weld seam preparation with maximum user safety by virtue of a dead-man switch and brake system
- One-touch controller: Patented, tool-free setting of the cutting depth in 0.1 steps; stop points for short setting times, and protection against unintentional adjustment of the cutting depth when working
- Precise setting of the chamfer angle directly via the guide plates
- Universal milling head with three carbide indexable inserts for all chamfer angles from 0-90°
- Controlled working by virtue of large-scale guide plates
- Stop roller to guide along pipes for easy preparation of weld seams
- Bail handle adjusts without tools for secure, even guiding
- Metabo Marathon-motor with patented dust protection for long service life
- Tacho Constamatic (TC) Full-wave Electronics: fast work progress by means of constant speed under load
- Patented, mechanical brake system stops the router bit within 2 seconds after switching off
- Electronic overload protection, soft start and restart protection
- Protection of the user by virtue of lateral plates for conveying the chips

Order no.	60175550
EAN code	4007430298416
No-load speed	12500 rpm
Rated input power	1550 W
Output power	840 W
Type of edges	Chamfer
Max. chamfer width 45°	14 mm / 9/16 "
Max. chamfer height at 45°	10 mm / 3/8 "
Grading of cutting depth setting	0.1 mm / 0.00394 "
Curves smallest outer Ø	75 mm / 2 15/16 "
Weight (without power cable)	5.1 kg / 11.2 lbs
Cable length	4 m / 13 ft

### Scope of delivery

3 Carbide indexable inserts Universal, Stop roller, Screwdriver for Torx screws 15, Screwdriver SW 4 with T-handle, Open-jawed spanner SW 10, Bow-type handle, Metal carry case