



## NMP 18 LTX BL M10

- Cordless rivet nut gun with setting power adjustment for blind rivet nuts up to M10 in aluminium, M8 in steel, M6 in stainless steel
- Versatile use thanks to mandrel quick change system
- Automatic drill-on of the blind rivet before setting
- Time-saving auto-reverse function: Pull mechanism returns to starting position after setting and nut is drilled off the mandrel
- Easy presetting of the placement force on the LED display for working that is gentle on the material and threads
- LED display with protective cover: 10 memory positions for retrievable settings
- Selectable LED light during setting or continuously (max. 10 min)
- Eyelet for energy-saving work with balancer / spring tension
- With matching adapter (accessory) also suitable for blind rivet studs
- Powerful Brushless motor for quick work progress and highest efficiency
- Practical storage screwed onto the housing for additional mandrels
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	601788850
EAN code	4061792212909
Battery voltage	18 V
Max. blind rivet nuts in aluminium	M 10
Max. blind rivet nuts in steel	M 8
Max. blind rivet nuts in stainless steel	M 6
Placement force	15 kN
Device travel	10 mm / 3/8 "
Weight without battery pack	2 kg
Weight with battery pack	2.4 kg

### Scope of delivery

Mandrels M4, M5 and M6, Mouthpieces M4, M5 and M6, Placement force information card, Hexagonal wrench, Open-end wrench, without battery pack, without charger