



ASR 36-18 BL 25 M SC with electromagnetic shaking

- Powerful cordless wet/dry vacuum cleaner with cordless control function for intelligent extraction without cable connection
- CordlessControl: the vacuum cleaner starts/stops automatically when the cordless tool from Metabo or other brands, which is connected to the hose, is switched on/shutting down
- Manual starting of the vacuum cleaner is also possible with the remote button at the coupling bush of the hose
- High suction power comparable to a mains-powered vacuum cleaner thanks to the energy of two 18 V or alternatively one 36V battery pack
- 3-stage suction power controller for adapted power depending on the application and maximum battery pack runtimes of more than 80 minutes
- High user safety: certified in accordance with EU standard for dust class M
- SelfClean: semi-automatic filter cleaning during breaks or manually when needed
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic function guaranteed exclusively with the electrical suction hose 630177000 included in the scope of delivery
- Uncluttered control panel with large rotary switches and battery pack capacity display
- Many details for safety and comfort: folding hose hook, rubberised storage surfaces and castors with brakes for safe stand
- Dust-proof and splash-proof battery pack compartment with lockable flap
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

| Order no. | 602046850 |
|-----------------------------|----------------------|
| EAN code | 4061792183544 |
| Type of battery pack | LiHD |
| Battery voltage | 18 V |
| Air output max. | 4000 l/min |
| Vacuum | 240 hPa (mbar) |
| Filter surface | 8600 cm ² |
| Container volume | 25 l |
| Suction hose Ø | 35 mm |
| Hose length | 4 m |
| Weight without battery pack | 12.3 kg / 27.1 lbs |
| Weight with battery pack | 13 kg / 28.7 lbs |

Scope of delivery

Suction hose 630177000 (Ø 35 mm / 4.0 m / electro-conductive), CordlessControl transmitter with fixing tape Ø 35 mm, 1 Multi tape, 2 Plastic suction tubes, Handle adapter, Fleece filter bag, 2 Polyester filter cassettes (M class), Floor nozzle (300 mm wide), Crevice nozzle, Coupling bush internal Ø 28 mm / external Ø 35 mm, without battery pack, without charger