



## ASR 25 L SC with Electromagnetic Shaking

- Compact vacuum cleaner for liquids and dry solids with commercial registration
- Ideal for mobile use due to low weight and compact construction
- For extraction from power tools and to clean construction sites, workshops etc.
- Power socket for a power tool for using the automatic start-up/shut-down of the vacuum cleaner
- SelfClean: semi-automatic filter cleaning during breaks for next use
- User protection: certified in accordance with EU standard for L class dust
- Automatic shut-down when vacuuming liquids once the maximum fill level is reached
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic basic equipment prevents static charge when using appropriate accessories
- Cable winding mechanism
- Practical accessory case and storage area
- Storage and transport system: coupling of MetaLoc and vacuum cleaner with the Metadepot (accessory)
- Two polyester filter cassettes with large filter area for constantly high suction capacity

Order no.	602024000
EAN code	4007430241054
Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm <sup>2</sup> / 1333 sq.inch
Input power max.	1400 W
Container volume	25 l / 7 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	3.2 m / 10 ft
Weight	11 kg / 24.3 lbs
Cable length	8 m / 26 ft

### Scope of delivery

Suction hose (Ø 35 mm / 3.2 m), Handle adapter, 2 Plastic suction tubes, 2 Polyester filter cassettes (M class), Fleece filter bag, Crevice nozzle, Universal Nozzle