



## ASR 50 M SC with Electromagnetic Shaking

- Compact vacuum cleaner for liquids and dry solids with commercial registration
- For extraction from power tools and to clean construction sites, workshops etc.
- Power socket for a power tool for using the automatical-start-up/shut-down of the vacuum cleaner
- SelfClean: semi-automatic filter cleaning during breaks for next use
- High user protection: certified in accordance with EU standard for M class dusts
- Automatic shut-down when vacuuming liquids once the maximum fill level is reached
- Warning signal on shortfall of the minimum volume flow to protect the user
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic basic equipment prevents static charge when using appropriate accessories
- Cable winding mechanism
- Practical accessory case and storage area
- Storage and transport system: coupling of MetaLoc and vacuum cleaner with the Metadepot (accessory)

<b>Order no.</b>	<b>602045000</b>
<b>EAN code</b>	<b>4007430241115</b>

Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm <sup>2</sup> / 1333 sq.inch
Input power max.	1400 W
Container volume	50 l / 13 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	4 m / 13 ft
Weight	16 kg / 35.3 lbs
Cable length	8 m / 26 ft

### Scope of delivery

Antistatic suction hose (Ø 35 mm / 4 m), Handle adapter, 2 Plastic suction tubes, 2 Polyester filter cassettes (M class), PE Filter bags, Fleece filter bag, Crevice nozzle, Universal Nozzle, Carrying handles